





PANEL CUT-OUT

Rating : 15A 125V AC T105 UL cUL
Insert And Extract Force: 1.36kgf~6.8kgf
Terminal Strength: ≥80N
Operating Life: ≥5000 cycles
Withstand Voltage: Between all terminals:2500VAC (50-60Hz)1min
terminals to Base:3750V AC (50-60Hz)1min
Leakage Current : 1mA
Insulation Resistance: ≥100MΩ 500V DC
Body Materil: NYLON 66 94V-2~0

序号	部品名称	材质	处理	数量	备注
1	DB-F-M2 塑胶件	PA66	黑色	1	
2	DB-F-MS 铜件	黄铜	镀锡	2	

A4				普通公差	深圳市华灿天禄电子有限公司					
A3				COMMON TOLERANCE :						
A2				UP TO 5	±0.20	单位	mm	投影	品名	Ac Inlet C14型
A1				ABOVE 5 TO 30	±0.30	UNIT		PROJECTED	PRODUCT NAME	比例
				ABOVE 30	±0.50	绘图	黄旭程	核对	型号	Free
				ANGULAR	±5°	DRAWN BY		CHECKED BY	MODEL NO.	DB-F
REV.	DATE	REVISION DESCRIPTION	ISSUE			日期	2015.07.27	核准	料号	DB-F-M2
						DATE		APPROVAL BY	PART NO.	