




ABIDE BY ROHS



PCB LAYOUT

使用温度范围 (Ambient temperature Range): $-25^{\circ} \sim +85^{\circ}$
适用线规 (Applicable Wires): AWG 30#~22#
适用基板厚度 (Applicable PCboard thickness): 1.6mm
额定电压 (Voltage rating): 250V AC, DC
额定电流 (Current rating): 3A
接触电阻 (Contact Resistance): $\leq 0.01 \Omega$
绝缘电阻 (Insulation Resistance): $\geq 1000 M\Omega$
耐压 (Withstand Voltage): 1000VAC/min
材料 (Material)
1. 基座: PA66 94V-0(2)
2. 插针: 黄铜

孔位	A-mm	B-mm
XH-2AW	7.5	2.5
XH-3AW	10.0	5.0
XH-4AW	12.5	7.5
XH-5AW	15.0	10.0
XH-6AW	17.5	12.5
XH-7AW	20.0	15.0
XH-8AW	22.5	17.5
XH-9AW	25.0	20.0
XH-10AW	27.5	22.5
XH-11AW	30.0	25.0
XH-12AW	32.5	27.5
XH-13AW	35.0	30.0
XH-14AW	37.5	32.5
XH-15AW	40.0	35.0
XH-16AW	42.5	37.5

2		Wafer 针	Brass Tin 黄铜镀锡	N	
1		Housing 基座	PA66 94V-0(2)	1	White 白色
序号	图号	名称	材料	数量	附注

ECN NO.	REV	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
---------	-----	-------	--------------	---------	--------	--------

单位 UNIT	mm	一般公差 TOLERANCE ARE				浙江恩盛电子有限公司 Zhejiang Ensheng Electronics Co., Ltd.			
绘图 DRAWN		$X.^{\circ} \pm 3^{\circ}$ $X.X^{\circ} \pm 5^{\circ}$				产品名称 TITLE	WAFERA针座		
设计 DESIGN		$>0-3$	$>3-18$	$>18-50$	$>50-120$	产品型号 MODEL	XH-NAW		
审核 CHECKED		± 0.12	± 0.15	± 0.3	± 0.5	产品编码 PART NO	ESWF-XHWOX-W-XX-C-B		
校准化 STANDARD		重量 WT.		视图 PROJ		比例 SCALE	:	页码 SHEET	1 OF 1
批准 APPROVALS		产地 PRODUCTION							