





ABIDE BY ROHS



ITEM	H±0.1	
01	7.3	√
02	7.5	



Circuit Diagram



PCB.circuit prohibited area



Remarks:

- 1.Rated current、Voltage: DC 12V 50mA
- 2.Contact resistance: $\leq 100\text{m}\Omega$
- 3.Insulation resistance: $\geq 100\text{M}\Omega$
- 4.The intensity of operations: $260\pm 50\text{gf}$
- 5.Life requirements: 100000次
- 6.Withstand voltage: AC 250V 1分钟
- 7.All materials comply with RoHS standards

5	Button	PPA	1	Black
4	Cover	Q195	1	Cu-Sn Plating
3	Shrapnel	SUS	1	Ag Plating
2	Housing	PPA	1	Black
1	Terminal	Brass	4	Ag Plating
NO.	PART NAME	MATERIAL	QTY	FINISHING

单位 UNIT	mm	一般公差 TOLERANCE ARE		浙江恩盛电子有限公司 Zhejiang Ensheng Electronics Co., Ltd.	
绘图 DRAWN		≤ 1	± 0.05		
设计 DESIGN		≤ 3	± 0.10	产品名称 TITLE	轻触开关
审核 CHECKED		≤ 5	± 0.15	产品型号 MODEL	6*6方头插脚
校准化 STANDARD		> 5	± 0.25	产品编码 PART NO	ES603X-10XX-73X-26-A
批准 APPROVALS		角度 ANGLE	$\pm 3^\circ$	视图 PROJ	比例 SCALE
				页码 SHEET	1 OF 1

ECN NO.	A	REV	DATE.	NEW	CHANGE.	CHECK.	APPRO.
				DESCRIPTION.			