







H	
4.3	4.5
5.0	5.5
6.0	6.5
7.0	7.5
8.0	8.5
9.0	9.5

主要技术规格:

1. 额定值: 50mA DC12V
2. 接触电阻: $\leq 50m\Omega$
3. 操作力: $160gf \pm 50gf$ & $250 \pm 50gf$
4. 行程: $0.3 \pm 0.1mm$
5. 绝缘电阻: $\geq 100M\Omega$
6. 抗电强度: 250V 50HZ 1Min.
7. 寿命: 100,000 Cycles
8. 防水等级: IP67
9. 防银迁移: 60V, 85℃, 90%RH/60H



电路图



PCB. 焊接图

序号	部件名称	材料	备注
1	按钮	PPA	耐温280℃ (黑色)
2	盖板	PPA	耐温280℃ (黑色)
3	防水垫	硅胶 (0.3mm)	耐温280℃ (黑色)
4	簧片	不锈钢	覆银
5	基座	PPA	耐温280℃ (黑色)
6	引脚、触点	黄铜	镀银

标记	处数	更改文件号	签名	日期
设计		Huang Hui		2019. 10. 09
审核		Mi Wei		2019. 10. 09
批准		Jack Guo		2019. 10. 09



连兴旺电子(深圳)有限公司

LXWCONN ELECTRONICS (SHENZHEN) CO., LTD

比例	一般公差	P/N: CTSMW6-043-R-V-0xx
单位	mm	
重量		
	角度	