







ABIDE BY ROHS

ITEM	H	
01	4.3	
02	5.0	
03	5.5	
04	6.0	
05	6.5	
06	7.0	
07	7.5	
08	8.0	
09	8.5	
10	9.0	
11	9.5	
12	10.0	
13	• • •	
14	15.0	







Circuit Diagram



P. C. B. Layout

Remarks:

1. Rated current, Voltage: DC 12V 50mA
2. Contact resistance: ≤50mΩ
3. Insulation resistance: ≥100MΩ
4. The intensity of operations: 260±50gf
5. Life requirements: 100000 times
6. Withstand voltage: AC250V 1 minute
7. All materials comply with RoHS standards



Remarks:

- 1, Braiding process, can not be caused by carrying half crushed;
- 2, Pay attention to the direction of the tape, with a clockwise direction out of the carrier tape, with a hole in the top or right

5	Button	PPA	1	Black
4	Cover	Q195	1	Cu-Sn Plating
3	Shrapnel	SUS	1	Ag Plating
2	Housing	PPA	1	Black
1	Terminal	Brass	4	Ag Plating
NO.	PART NAME	MATERIAL	QTY	FINISHING

单位 UNIT	mm	一般公差 TOLERANCE ARE		浙江恩盛电子有限公司 Zhejiang Ensheng Electronics Co., Ltd.	
绘图 DRAWN		X≤1	±0.05		
设计 DESIGN		1≤X≤5	±0.10	产品名称 TITLE	轻触开关
审核 CHECKED		5≤X≤10	±0.15		
校准化 STANDARD		X>10	±0.25	产品型号 MODEL	12*12*H贴片
批准 APPROVALS		重量 WT.		产品编码 PART NO	ES1202-10XX-XXX-26-B
		产地 PRODUCTION		视角 PROJ	比例 SCALE
					页码 SHEET
					1 OF 1

ECN NO.	REV	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
---------	-----	-------	--------------	---------	--------	--------