



NOTE:

1. ALL DIMENSIONS ARE IN MILLIMETERS, BRACKETED DIMENSIONS ARE IN INCHES.

2. GENERAL TOLERANCES MAX. $\pm 0.2\text{mm}$



REV	DESCRIPTION	DRW	DATE



P.C.B DIMENSION (TOP VIEW)

SPECIFICATIONS

- Rating : 100mA, DC 42V (Switching)
400mA, DC 42V (None-Switching)
- Contact Resistance : 80m Ω Max.
- Insulation Resistance : 100M Ω Min at DC 250V
- Operating Force : 120 $\pm$ 30gf Max.
- Life Cycle : 25,000 steps
- Sealing : IP67 (Dust & Water proof)



		Real Coded				
10 P o s i t i o n		C	1	2	4	8
	0	●				
	1	●	●			
	2	●		●		
	3	●	●	●		
	4	●			●	
	5	●	●		●	
	6	●		●	●	
	7	●	●	●	●	
	8	●				●
16 P o s i t i o n	9	●	●			●
	A	●		●		●
	B	●	●	●		●
	C	●			●	●
	D	●	●		●	●
	E	●		●	●	●
	F	●	●	●	●	●

本公司智慧財產，未經同意不得複製
Without permission, copying is
strictly prohibited.

設計	Huang Hui	±位	mm	材料	12/04/30	 连兴旺电子(深圳)有限公司 LXWCONN ELECTRONICS (SHENZHEN) CO., LTD			
校對	Mi Wei	全週倒角		數量					
審核	Jack Kuo	視圖		處理		圖號	RBMSDR-10	機型	RB Series
						設備		圖名	Rotary Switch