





修	記號	g	容	修改者	日期
改	1				
	2				



Specification

- Rating** : Voltage 42V 100mA (Switching)
400mA (None-Switching)
- Contact Resistance** : 80mΩ Max
- Insulation Resistance**: 100MΩ Min
- Operating Force** : 120gf±30gf
- Life Cycle**: 25,000 steps
- Solder Condition** : Reflow Soldering : 10s/260 °C
Iron Soldering : 3s/350°C
Wave Soldering : 5s/280°C

		Real Code				
		C	1	2	4	8
10 Positions	0	●				
	1	●	●			
	2	●		●		
	3	●	●	●		
	4	●			●	
	5	●	●		●	
	6	●		●	●	
	7	●	●	●	●	
	8	●				●
	9	●	●			●
16 Positions	A	●		●		●
	B	●	●	●		●
	C	●			●	●
	D	●	●		●	●
	E	●		●	●	●
	F	●	●	●	●	●

本公司智慧財產，未經同意不得複製
Without permission, copying is
strictly prohibited.

中心孔距
皆為±0.05

一般公差
0~ 150 : ±0.05
>151~ 300 : ±0.1
>301~ 500 : ±0.2
>501~1000 : ±0.3

製圖

P.M.D

比例

5:1

日期

15/11/05

設計

Shane jin

單位

mm

材質

校對

Boris jia

全週倒角

數量

審核

Jack Kuo

視圖



處理



连兴旺电子(深圳)有限公司

LXWCONN ELECTRONICS (SHENZHEN) CO., LTD

圖號

RBMSDR-16S

機型

RB

Series

設備

圖名

備註: