







ITEM	H	
01	4.3	
02	4.5	
03	5.0	
04	5.5	
05	6.0	
06	6.5	
07	7.0	
08	8.0	
09	9.0	
10	...	
11	13.0	



Circuit diagram



PCB Layout

1. Rated current, Voltage: DC 12V 50mA
2. Contact resistance: $\leq 100\text{m}\Omega$
3. Insulation resistance: $\geq 100\text{M}\Omega$
4. The intensity of operations: $260 \pm 50\text{gf}$
5. Life requirements: 100000 times
6. Withstand voltage: AC 250V 1 minute
7. All materials comply with RoHS standards

5	Button	PPA	1	Black
4	Cover	Q195	1	Cu-Sn Plating
3	Shrapnel	SUS301	1	Ag Plating
2	Housing	PPA	1	Black
1	Terminal	Brass	2	Ag Plating
NO.	PART NAME	MATERIAL	QTY	FINISHING

单位 UNIT	mm	一般公差 TOLERANCE ARE		 浙江恩盛电子有限公司 Zhejiang Ensheng Electronics Co., Ltd.	
绘图 DRAWN		$X \leq 1$	± 0.05		
设计 DESIGN		$1 \leq X \leq 5$	± 0.10	产品名称 TITLE	轻触开关
		$5 \leq X \leq 10$	± 0.15		
		$X > 10$	± 0.25		
审核 CHECKED		图号 DRAWING NO	——	产品型号 MODEL	6*6边二脚
核准化 STANDARD		重量 WT.		产品编码 PART NO	ES606X-10XX-XXX-26-A
批准 APPROVALS		产地 PRODUCTION		视角 PROJ	 比例 SCALE : 页码 SHEET 1 OF

_____	A	_____	NEW	_____	_____	_____
ECN NO.	REV	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.