








ABIDE BY ROHS



P. C. B. Layout



Circuit Diagram

Remarks:

- 1.Rated current、Voltage: DC 12V 50mA
- 2.Contact resistance: $\leq 100\text{m}\Omega$
- 3.Insulation resistance: $\geq 100\text{M}\Omega$
- 4.The intensity of operations: $260\pm 50\text{gf}$
- 5.Life requirements:100000次
- 6.Withstand voltage: AC 250V 1分钟
- 7.All materials comply with RoHS standards

5	Button	PPA	1	Black
4	Shrapnel	SUS301	1	Ag Plating
3	Bracket	Q195	1	Cu-Sn Plating
2	Housing	PPA	1	Black
1	Terminal	Brass	2	Ag Plating
NO	PART NAME	MATERIAL	QTY	FINISHING

单位 UNIT	mm	一般公差 TOLERANCE ARE		浙江恩盛电子有限公司 Zhejiang Ensheng Electronics Co., Ltd.	
绘图 DRAWN		$X \leq 1$	± 0.05		
设计 DESIGN		$1 \leq X \leq 5$	± 0.10	产品名称 TITLE	轻触开关
审核 CHECKED		$5 \leq X \leq 10$	± 0.15		
校准化 STANDARD		$X > 10$	± 0.25	产品型号 MODEL	6*6方头支架
批准 APPROVALS		重量 WT.		产品编码 PART NO	ES635X-10XX-73X-26-A
		产地 PRODUCTION		视角 PROJ	
				比例 SCALE	:
				页码 SHEET	1 OF 1

ECN NO.	REV	DATE.	NEW DESCRIPTION.	CHANGE.	CHECK.	APPRO.
---------	-----	-------	---------------------	---------	--------	--------