








H	
3.1	3.5
4.3	4.5
5.2	




PCB. 焊接图

主要技术规格:

1. 额 定 值: 50mA DC12V
2. 接触电阻: $\leq 50\text{m}\Omega$
3. 操 作 力: $250\pm 40\text{gf}$
4. 行 程: $0.25\pm 0.1\text{mm}$
5. 绝缘电阻: $\geq 100\text{M}\Omega$
6. 抗电强度: 250V 50HZ 1Min.
7. 寿 命: 100,000 Cycles



电 路 图

										第一视角 				名称：轻触开关			
5	引脚、触点	黄铜	1	镀银										型号：CTSMW-67R-V-0xx			
4	基座	PPA	1	耐温280℃													
3	簧片	不锈钢	1	覆银	标记	处数	更改文件号	签 名	日 期	比 例		一般公差		连兴旺电子(深圳)有限公司 LXWCONN ELECTRONICS(SHENZHEN)CO.,LTD			
2	盖板	冷轧钢	1		设 计		朱余东	2016. 05. 10	单 位	mm	0. 5~2	±0. 10					
1	按钮	硅胶	1	耐温280℃（蓝色）	审 核		樊剑森	2016. 05. 10	重 量		2~5	±0. 25					
											5~10	±0. 30					
											角度	±0. 5°					
序号	零件名称	材料规格	数量	备注	批 准		夏兴祥	2016. 05. 12									