





ABIDE BY ROHS

ITEM	H	
01	4.0	
02	4.3	
03	4.5	
04	4.8	
05	5.0	
06	5.5	
07	6.0	
08	6.5	
09	7.0	
10	7.3	
11	7.5	
12	8.0	
13	8.5	
14	...	
15	20.0	



* Key size



开关示意图



PCB.circuit prohibited area



Remarks:

- 1.Rated current、Voltage: DC 12V 50mA
- 2.Contact resistance: $\leq 100\text{m}\Omega$
- 3.Insulation resistance: $\geq 100\text{M}\Omega$
- 4.The intensity of operations: $160\pm 50\text{gf}$
- 5.Life requirements:100000次
- 6.Withstand voltage: AC 250V 1分钟
- 7.All materials comply with RoHS standards

5	Button	PPA	1	Black
4	cover	SPCC	1	Copper tin
3	Shrapnel	SUS301	1	Silver coating
2	Base	PPA	1	Black
1	TERMINAL	Brass	4	Ag Plated
NO.				

单位 UNIT	mm	一般公差 TOLERANCE ARE		浙江恩盛电子有限公司 Zhejiang Ensheng Electronics Co., Ltd.	
绘图 DRAWN		≤ 5	± 0.2	产品名称 TITLE	轻触开关
设计 DESIGN		5~30	± 0.3		
审核 CHECKED		30~50	± 0.4		
校准化 STANDARD		>50	± 0.5	产品型号 MODEL	6*6*H贴片
批准 APPROVALS		重量 WT.		产品编码 PART NO	ES602X-10XX-XXX-16-B
		产地 PRODUCTION		视角 PROJ	比例 SCALE
					页码 SHEET
					1 OF 1