







1. FPC NOT MATING CONDITION BANNED CLOSURE
2. ALL MATERIAL MUST BE COMPLY WITH ROHS




3D

NOTE: ALL RIGHTS RESERVED,BANNED COPY!

SCALE=2/1



Applicable FPC



Recommended P.C.B Layout

NO POSITIONS	A	B	C	D
9PIN	4.30	3.10	1.80	2.40
11PIN	4.90	3.70	2.40	3.00
13PIN	5.50	4.30	3.00	3.60
15PIN	6.10	4.90	3.60	4.20
17PIN	6.70	5.50	4.20	4.80
19PIN	7.30	6.10	4.80	5.40
21PIN	7.90	6.70	5.40	6.00
23PIN	8.50	7.30	6.00	6.60
25PIN	9.10	7.90	6.60	7.20
27PIN	9.70	8.50	7.20	7.80
29PIN	10.30	9.10	7.80	8.40
31PIN	10.90	9.70	8.40	9.00
33PIN	11.50	10.30	9.00	9.60
35PIN	12.10	10.90	9.60	10.20
39PIN	13.30	12.10	10.80	11.40
41PIN	13.90	12.70	11.40	12.00
45PIN	15.10	13.90	12.60	13.20
51PIN	16.90	15.70	14.40	15.00
55PIN	18.10	16.90	15.60	16.20
57PIN	18.70	17.50	16.20	16.80
61PIN	19.90	18.70	17.40	18.00
67PIN	21.70	20.50	19.20	19.80
71PIN	22.90	21.70	20.40	21.00

NO.	COMPONENTS	MATERIALS	COLOR/SPECIFICATION	QUANTITY
1	HOUSING	LCP	BLACK UL94V-0	1 PCS
2	COVER	PA9T	BLACK UL94V-0	1 PCS
3	CONTACT	PHOSPHOR BRONZE	T=0.12mm PLATING	POSITIONS
4	CONTACT	PHOSPHOR BRONZE	T=0.12mm PLATING	POSITIONS
5	STATOR	BRASS	T=0.15mm PLATING	2 PCS

修订 SER	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE

UNLESS OTHERWISE
SPECIFIED TOLERANCE
ANG TOL DIM TOL
X ±2.0° X ±0.20
XX ±1.0° XX ±0.10
XXX ±0.5° XXX ±0.05

版本 (REV) A



LXW 连兴旺电子(深圳)有限公司
connectivity LXWCONN ELECTRONICS (SHENZHEN) CO., LTD

制图 (DR): Jerry 2020.04.10	品名(TITLE): FPC 0.3PITCH H0.9 BACK FLIP TYPE CONNECTOR
审核 (CHKD):	料号(PART NO): LXW-FPC35C-NS-0.3SH-01
核准 (APPD): Tong 2020.04.10	比例(SCALE): 1:1 单位(UNITS): mm 张数(SHEET): 1 OF 1 图幅(SIZE): A4