



UL Standard

Use group	B	C	D
Rated Current	8A	/	/
Rated Voltage	300V	/	/

IEC Standard

1. Pollution Degree	3	2	2
Overvoltage Category	III	III	II
Rate Impulse Voltage(KV)	2.5KV	2.5KV	2.5KV
Rate Voltage(V)	160V	160V	250V
Rate Current(A)	8A	8A	8A

NOTES2:

- 1.Housing: PA66 (UL94V-0)
- 2.Long Solder Pin: Brass (Sn Plated)
- 3.Short Solder Pin: Brass (Sn Plated)

NOTES3:

- 1.Pitch: 3.5mm Poles: 2x(02-24)P
2.Operating temperature: -40℃~+105℃
3.RoHS Compliance

How to order

MX15EDGRHB - 3.5 - 2xXXP - XXXX - X - X

产品型号 间距 极数 01:常规颜色 02-99: 定制颜色 A-Z其他定制

颜色: 灰色:GY 橙色:OE 定制颜色 Cu:铜
蓝色:BU 红色:RD Fe:铁
黑色:BK 透明色:TT
绿色:GN 黄色:YW
白色:WE

Pitch Range In mm			Nominal Dimension Range In mm					—		
TO 6	Over 6 TO 10	Over 10 TO 24	TO 30	Over 30 TO 60	Over 60 TO 100	Over 100 TO 150	Over 150	0.1/10		
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2*		

ITEM	NAME OF PART		NO. OF PART	Q"TY	MATERIAL		NOTE	
DWG.	CKK	DATE	24.07.25	UNITS	MM	SHEET/OF	1/1	
CHK.		DATE		SCALE	1:1	A4		
APP.		DATE			MX15EDGRHB-3.5-2xXXP			
 CIXI MAIXU ELECTRONICS CO., LTD. 慈溪市迈旭电子有限公司				NAME				
				DWGNO.				