







ABIDE BY ROHS




PCB LAYOUT

Remarks:

1. Rated current、Voltage: DC 12V 50mA
2. Contact resistance: $\leq 100\text{m}\Omega$
3. Insulation resistance: $\geq 100\text{M}\Omega$
4. The intensity of operations: $160 \pm 50\text{gf}$
5. Life requirements: 100000次
6. Withstand voltage: AC 250V 1分钟
7. All materials comply with RoHS standards

5	Button	PPA	1	Black
4	Cover	Q195	1	Cu-Sn Plating
3	Shrapnel	SUS	1	Ag Plating
2	Housing	PPA	1	Black
1	Terminal	Brass	2	Ag Plating
NO.	PART NAME	MATERIAL	QTY	FINISHING

单位 UNIT	mm	一般公差 TOLERANCE ARE		 浙江恩盛电子有限公司 Zhejiang Ensheng Electronics Co., Ltd.	
绘图 DRAWN		$X \leq 1$	± 0.05		
设计 DESIGN		$1 \leq X \leq 5$	± 0.10	产品名称 TITLE	轻触开关
审核 CHECKED		$5 \leq X \leq 10$	± 0.15		
校 STANDARD		$X > 10$	± 0.25	产品型号 MODEL	6*6*7.3方头贴片
批准 APPROVALS		图号 DRAWING NO		产品编码 PART NO	ES604X-10XX-73X-16-B
		重量 WT.		视角 PROJ	
		产地 PRODUCTION		比例 SCALE	:
				页码 SHEET	1 OF 1

ECN NO.	A	NEW	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
---------	---	-----	--------------	---------	--------	--------