

5

4




3

2




1

ABIDE BY ROHS

ITEM	H	
01	4.3	
02	5.0	
03	5.5	
04	6.0	
05	6.5	
06	7.0	
07	7.5	
08	8.0	
09	8.5	
10	9.0	
11	9.5	
12	10.0	
13	...	
14	20.0	



P. C. B. Layout



Circuit Diagram

Remarks:

- 1.Rated current、Voltage: DC 12V 50mA
- 2.Contact resistance: $\leq 100\text{m}\Omega$
- 3.Insulation resistance: $\geq 100\text{M}\Omega$
- 4.The intensity of operations: $260\pm 50\text{gf}$
- 5.Life requirements: 100000 times
- 6.Withstand voltage: AC 250V 1 minute
- 7.All materials comply with RoHS standards


5	Button	PPA	1	Black
4	Cover	Q195	1	Cu-Sn Plating
3	Shrapnel	SUS	1	Ag Plating
2	Housing	PPA	1	Black
1	Terminal	Brass	4	Ag Plating
NO.	PART NAME	MATERIAL	QTY	FINISHING

单位 UNIT	mm	一般公差 TOLERANCE ARE		浙江恩盛电子有限公司 Zhejiang Ensheng Electronics Co., Ltd.	
绘图 DRAWN		$X \leq 1$	± 0.05		
设计 DESIGN		$1 \leq X \leq 5$	± 0.10	产品名称 TITLE	
审核 CHECKED		$5 \leq X \leq 10$	± 0.15		
		$X > 10$	± 0.25	产品型号 MODEL	
校准化 STANDARD		重量 WT.			
批准 APPROVALS		产地 PRODUCTION		产品编码 PART NO	

浙江恩盛电子有限公司
Zhejiang Ensheng Electronics Co., Ltd.

轻触开关

12*12插脚圆头

比例
SCALE

:

页码
SHEET

1 OF 1

D

D

C

C

B

B

A

A

ECN NO.	REV	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
---------	-----	-------	--------------	---------	--------	--------

5

4

3

2

1