




ABIDE BY ROHS



ITEM	H	
01	3.8	
02	4.3	
03	4.5	
04	4.8	
05	5.0	
06	5.5	
07	6.0	
08	6.5	
09	7.0	
10	7.5	
11	8.0	
12	...	
13	10.0	



CIRCUIT DIAGRAM



PCB.circuit prohibited area



- Remarks:
- 1.Rated current、Voltage: DC 12V 50mA
 - 2.Contact resistance: $\leq 100\text{m}\Omega$
 - 3.Insulation resistance: $\geq 100\text{M}\Omega$
 - 4.The intensity of operations: $260 \pm 50\text{gf}$
 - 5.Life requirements: 100000 times
 - 6.Withstand voltage: AC250V 1 minute
 - 7.All materials comply with RoHS standards

E	Terminal	Brass	2	Ag Plating
C	Shrapnel	SUS	1	Ag Plating
D	Housing	PPA	1	Black
B	Cover	Q195	1	Cu-Sn Plating
A	Button	PPA	1	Black
NO.	PART NAME	MATERIAL	QTY	FINISHING
单位 UNIT	mm	一般公差 TOLERANCE ARE	浙江恩盛电子有限公司 Zhejiang Ensheng Electronics Co., Ltd.	
绘图 DRAWN		X ≤ 1 ± 0.05		
设计 DESIGN		1 ≤ X ≤ 5 ± 0.10	产品名称 TITLE	轻触开关
审核 CHECKED		5 ≤ X ≤ 10 ± 0.15	产品型号 MODEL	4.5*4.5边三脚
校准化 STANDARD		X > 10 ± 0.25	产品编码 PART NO	ES413X-10XX-XXX-26-A
批准 APPROVALS		重量 WT.	视角 PROJ	
		产地 PRODUCTION	比例 SCALE	: 页码 SHEET
				1 OF 1

ECN NO.	REV	DATE.	NEW	CHANGE.	CHECK.	APPRO.
			DESCRIPTION.			