







ABIDE BY ROHS



PCB LAYOUT

Remarks:

1. Rated current、Voltage: DC 12V 50mA
2. Contact resistance: $\leq 100\text{m}\Omega$
3. Insulation resistance: $\geq 100\text{M}\Omega$
4. The intensity of operations: $250 \pm 50\text{gf}$
5. Life requirements: 100000次
6. Withstand voltage: AC 250V 1分钟
7. All materials comply with RoHS standards

5	Button	PPA	1	Black
4	Cover	Q195	1	Cu-Sn Plating
3	Shrapnel	SUS	1	Ag Plating
2	Housing	PPA	1	Black
1	Terminal	Brass	2	Ag Plating
NO.	PART NAME	MATERIAL	QTY	FINISHING
单位 UNIT	mm	一般公差 TOLERANCE ARE		
绘图 DRAWN		$X \leq 1$	± 0.05	浙江恩盛电子有限公司 Zhejiang Ensheng Electronics Co., Ltd.
设计 DESIGN		$1 \leq X \leq 5$	± 0.10	
审核 CHECKED		$5 \leq X \leq 10$	± 0.15	
校准化 STANDARD		$X > 10$	± 0.25	产品名称 TITLE
批准 APPROVALS		图号 DRAWING NO	产品型号 MODEL	轻触开关
		重量 WT.	产品编码 PART NO	6*6*7.3方头贴片
		产地 PRODUCTION	视角 PROJ	ES604X-10XX-73X-26-B
			比例 SCALE	
			页码 SHEET	1 OF 1