








SECTION:A-A



PANEL CUT-OUT



PANEL THICKNESS	X
1.0	20
1.2	20
2.0	21
2.5	21

Rating :
15A 250V AC UL cUL
10A 250V AC 3C VDE KC

Insert And Extract Force: 1.36kgf~6.8kgf

Terminal Strength: $\geq 80N$

Operating Life: ≥ 5000 cycles

Withstand Voltage: Between all terminals:2000VAC (50-60Hz)1min

terminals to Base:3750V AC (50-60Hz)1min

Leakage Current : 1mA

Insulation Resistance: $\geq 100M\Omega$ 500V DC

Body Materil: NYLON 66 94V-0

A4				普通公差	深圳市华灿天禄电子有限公司					
A3				COMMON TOLERANCE :						
A2				UP TO 5	± 0.20	单位	mm	投影	品名	Ac Inlet C14型
A1				ABOVE 5 TO 30	± 0.30	UNIT		PROJECTED	PRODUCT NAME	比例
REV.	DATE	REVISION DESCRIPTION	ISSUE	ABOVE 30	± 0.50	绘图	金泽木	核对	型号	Free
				ANGULAR	$\pm 5^\circ$	DRAWN BY		CHECKED BY	料号	DB-14
						日期	2021/8/4	核准	PART NO.	DB-14-2 F
						DATE		APPROVAL BY		