








P. C. B LAYOUT TOP VIEW

PIN	Ø 2.0	Ø 2.5
APPO		

DIMENSION CLASSIFICATION

■ : CRITICAL
 ☒ : MAJOR

TOLERANCE TABLE

.X	±	0.40
.XX	±	0.25
.XXX	±	0.10
ANGLE	±	2°

台灣碩方精密電子科技有限公司
 TAIWAN SOFNG PRECISION ELECTRONIC CO., LTD

TITLE
 DC-012A-T20
 立式DIP电源插座

PART NO. DC-012A-T20

APPROVED Peck DWG NO. DC-012A

CHECKED Paul SCALE 1:1 UNIT mm SIZE A4

DRAWIN David REV AO SHEET NO. 1/1



開關, 連接器
 SoFNG



邀您使用(微信)小程序
 碩方电子开关&连接器选型手册
 手机扫码即可进入...

主要技术性能	公差
额定电负荷 DC 30V\0.5A	X. ±0.20
接触电阻 ≤0.03Ω	. X ±0.10
绝缘电阻 ≥100MΩ	. XX ±0.05
耐压 AC500V (50Hz)/min	. XXX ±0.02
插拔力 3-20N	X* ±5°
使用温度范围 -30~70℃	. X* ±2°
使用寿命 5000次	. XX* ±1°

