








P. C. B LAYOUT TOP VIEW

PIN	Ø 2.0	Ø 2.5
APPO		

DIMENSION CLASSIFICATION		台灣碩方精密電子科技有限公司 TAIWAN SOFNG PRECISION ELECTRONIC CO., LTD			
: CRITICAL : MAJOR		TITLE DC-012A-T25 立式DIP电源插座 開關, 連接器 SOFNG			
TOLERANCE TABLE					
.X	± 0.40	PART NO.	DC-012A-T25		SERIES SD106
.XX	± 0.25	APPROVED	Peck	DWG NO.	DC-012A
.XXX	± 0.10	CHECKED	Paul	SCALE 1:1	UNIT mm SIZE A4
ANGLE	± 2°	DRAWIN	David	REV AO	SHEET NO. 1/1

主要技术性能		公差
额定电负荷	DC 30V\0.5A	X. ±0. 20
接触电阻	≤0.03Ω	. X ±0. 10
绝缘电阻	≥100MΩ	. XX ±0. 05
耐 压	AC500V (50Hz)/min	. XXX ±0. 02
插 拔 力	3-20N	X* ±5°
使用温度范围	-30~70℃	. X* ±2°
使用寿命	5000次	. XX* ±1°



邀您使用(微信)小程序
硕方电子开关&连接器选型手册
手机扫码即可进入...

