







ROHS



PCB Layout Diagram
Bottom View

- 技术要求:
- 1、截断面毛刺高度 $\leq 0.03\text{mm}$;
 - 2、要求平整,无变形、裂纹、损伤等外观缺陷;

1	TERMINAL +	1	Mn Steel T=0.25	Ni-Plating	
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR	
COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司			
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
CHECK					
APPROVAL					
TOLERANCES ARE		TITLE	电池扣CR927	REV. A	
30-150	±0.35	PART NO.	LAIL-CR927-M0-01	UNITS mm	
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				
ANGLE		DWG.NO.	Projection 		
±3°					