








Rating :

15A 250V AC T105 UL cUL
10A 250V AC VDE 3C KC

Insert And Extract Force: 1.36kgf~6.8kgf

Terminal Strength: $\geq 80N$

Operating Life: ≥ 5000 cycles

Withstand Voltage: Between all terminals:2500VAC (50-60Hz)1min
terminals to Base:3750V AC (50-60Hz)1min

Leakage Current : 1mA

Insulation Resistance: $\geq 100M\Omega$ 500V DC

Body Materil: PBT 94V-2-0

A4				普通公差	深圳市华灿天禄电子有限公司				
A3				COMMON TOLERANCE :					
A2				UP TO 5	±0.20	单位	mm	投影	品名
A1				ABOVE 5 TO 30	±0.30	绘图	吴瑜	核对应	Ac Inlet C14型
				ABOVE 30	±0.50	日期	2013.07.16	核准	比例
REV.	DATE	REVISION DESCRIPTION	ISSUE	ANGULAR	±5°	DATE	2013.07.16	APPROVAL BY	Free
					DB-14				
					DB-14-13P				