







RoHS

目錄
MAPX设变内容
MODIFICATION日期
DATE

RECOMMENDED PCB LAYOUT



电气特性:Electrical:

1. 额定电流: Current Rating
1.5A/contact terminal
 2. 额定电压: Voltage Rating
30V DC
 3. 接触阻抗: Contact Resistance
30 milliohms MAX
 4. 耐电压: Dielectric Withstanding Voltage:
500 V AC AT Sea Level
 5. 绝缘阻抗: Insulation Resistance:
1000MEGA ohms MIN
- 物理性能: Mechanical:
1. 插拔力: Connector Mate and Unmate Force
Mate force: 3.57kgf (MAX)
Unmate force: 0.7kgf (MIN)
 2. 端子保持力: Terminal Retention
1.0kgf (MIN)
 3. 寿命: 1500次
- 原材料: Material:
1. 塑胶: Housing: pbt /lcp
 2. 端子: Contact: Copper Alloy C2680
 3. 外壳: Shell: SPCC/c2680
- 电镀: Finish:
1. 端子 Contact: Au G/F u" Plated on contact area
Tin50u" Plated on solder area
Nickel 30u" Plated underplating over all.
 2. 外壳 Shell: Nickel 50u" Min plating over all.
 3. Temperature Range: -55° C to +85° C

Pin NUMBER	SIGNAL NAME
1	VBUS
2	D-
3	CC
4	D+
5	GND

产品图 PRODUCT CHART DWG			
公差一览表 TOLERANCE UNLESS OTHERWISE			
X.	±0.35	X'.	±5°
.X	±0.30	.X'	±2°
.XX	±0.25	.XX'	±1°
.XXX	±0.10	.XXX'	±0.5°

单位 UNITS		MM	制图 DRAWING	Erick	产品料号 PRODUCT PART NO.	905-761A3022S10200
比例 SCALE		1:1	审核 CHKD	L S S	产品名称 PRODUCT NO.	AF大电流11.0沉板1.9四脚插板无边 铁壳PA9T黑胶贴板/SPIN
日期 DATE		2021/03/10	核准 APPD	翻版	画法 VIEW	版本 VER
						A0

深圳市精拓金电子有限公司
Shenzhen Jing Tuo Jin Electronics Co., Ltd.