






ROHS



PCB Layout Diagram
Top View



NOTE:

1.MATERIAL:

a.HOUSING:PA66

b.CONTACT:BRASS

(SURFACE PLATING: Ni-PLATING)

SEE ORDERING

INFORMATION

2.ELECTRIC:

a.CONTACT RESISTANCE: 100 MILLIOHMS MAX

b.INSULATION RESISTANCE: 100 MEGA OHMS

MIN

c.DIELECTNIC VOLTAGE: 500V AC ONE MINUTE


d.OPERATING TEMPERATURE: -25°C~ +85°C

3.PACKAGING:

a.PLASTIC TRAY(PLEASE REFER TO PAGE TWO



FOR

DETAILS)




3	TERMINAL(-)	1	BRASS, T=0.25mm	Ni-Plating
2	TERMINAL(+)	1	BRASS, T=0.25mm	Ni-Plating
1	HOUSING	1	PA66	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR
COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司		
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO.,LTD		
CHECK				
APPROVAL				
TOLERANCES ARE				
30-150	±0.35	ANGLE	TITLE	
10-30	±0.2		电池座适用电池规格CR2032	
5-10	±0.15		REV.	
0-5	±0.1		A	
±3°		PART NO.	LAIL-CR2032-DIP90-B03-1BJ	UNITS
		DWG.NO.		mm
				Projection

REV.	ECN NO.	DESCRIPTION	DRAW	DATE



Packaging information:

1. Each plate contains 7 rows, each row contains 10 PCS, for a total of 70 PCS;
2. 22 plastic plates are tied together and covered with a lid at the top, totaling 1540 products;
3. Each large plastic bag contains two bundles of 44 plates of products, totaling 3080 products;
4. Each outer box contains a large plastic bag, totaling 3080 products;
5. Seal the top and bottom of the outer box with adhesive tape to form the character “工”;



COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD			
DRAWING						
CHECK						
APPROVAL						
TOLERANCES ARE			TITLE	电池座适用电池规格CR2032	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-CR2032-DIP90-B03-1BJ	UNITS	mm
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
			DWG.NO.			