






ROHS



PCB Layout Diagram
Top View

1.MATERIAL:

- a.HOUSING:PPS UL94V-0
- b.CONTACT:PHOSPHOR BRONZE
(SURFACE PLATING:Au1u")

SEE ORDERING INFORMATION

2.ELECTRIC:

- a.CONTACT RESISTANCE: 30 MILLIOHMS MAX
- b.INSULATION RESISTANCE: 100 MEGA OHMS MIN
- c.DIELECTNIC VOLTAGE: 500V AC ONE MINUTE
- d.OPERATING TEMPERATURE: -25°C~ +85°C

3	TERMINAL(-)	1	PHOSPHOR BRONZE, T=0.20	Gold Plating and Ni Under-Plating
2	TERMINAL(+)	1	PHOSPHOR BRONZE, T=0.20	Gold Plating and Ni Under-Plating
1	HOUSING	1	PPS	BROWN
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR

COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
DRAWING		TITLE 电池底座适用电池规格CR1220 REV. A			
CHECK					
APPROVAL					
TOLERANCES ARE		PART NO. LAIL-CR1220-SMT-B02-3AA	UNITS mm	DWG.NO.	Projection 
30-150	±0.35				
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				
ANGLE ±3°					