





PANEL CUT-OUT

Rating :
 5A 250V AC T105 UL cUL
 2.5A 250V AC VDE 3C KC
 Insert And Extract Force: 1.36kgf~6.8kgf
 Terminal Strength: $\geq 80N$
 Operating Life: ≥ 5000 cycles
 Withstand Voltage: Between all terminals: 2500VAC (50-60Hz) 1min
 terminals to Base: 3750V AC (50-60Hz) 1min
 Leakage Current : 1mA
 Insulation Resistance: $\geq 100M\Omega$ 500V DC
 Body Material: PBT 94V-2-0

序号	部品名称	材质	处理	数量	备注
1	DB-8-7 塑胶件	PBT	黑色	1	
2	DB-8-1DX 插销	黄铜	镀镍	2	
3	DB-8-S1 端子	黄铜	镀锡	2	

A4				普通公差	深圳市华灿天禄电子有限公司				
A3				COMMON TOLERANCE :					
A2				UP TO 5	±0.20	单位	mm	投影	品名
A1				ABOVE 5 TO 30	±0.30	绘图	黄旭程	核对应	Ac Inlet C8型
REV.	DATE	REVISION DESCRIPTION	ISSUE	ANGULAR	±5°	日期	2014.09.19	核准	比例
					Free				
					DB-8				
					DB-8-7S1				