







ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE



- NOTE:
- 1.MATERIAL:
- a.HOUSING:PPA BROWN
 - b.CONTACT:PHOSPHOR BRONZE (SURFACE PLATING: Au1u")
- SEE ORDERING INFORMATION
- 2.ELECTRIC:
- a.CONTACT RESISTANCE: 30 MILLIOHMS MAX
 - b.INSULATION RESISTANCE: 100 MEGA OHMS MIN
 - c.DIELECTNIC VOLTAGE: 500V AC ONE MINUTE
 - d.OPERATING TEMPERATURE: -25° C~ +85° C



PCB Layout Diagram
Top View

3	TERMINAL(-)	1	C5191 T=0.20MM	Au(1u")-Plating
2	TERMINAL(+)	1	C5191 T=0.25MM	Au(1u")-Plating
1	HOUSING	1	PPA	BROWN
NO.	PART NAME	Q'TY	MATERIAMATERIAL	PLATING & COLOR
COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司		
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO.,LTD		
CHECK				
APPROVAL				
TOLERANCES ARE				
30-150	±0.35	ANGLE		
10-30	±0.2			
5-10	±0.15			
0-5	±0.1			
		±3°		
TITLE		电池座适用电池规格CR2032		REV. A
PART NO.		LAIL-CR2032-SMT-B07-2AA		UNITS mm
DWG.NO.				Projection