

ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

NOTE:

1.MATERIAL:

a.HOUSING:PBT UL94 V-0 BLACK

b.CONTACT:PHOSPHOR BRONZE

(SURFACE PLATING: Ni100U"~120U")

SEE ORDERING INFORMATION






2.ELECTRIC:

a.CONTACT RESISTANCE: 100 MILLIOHMS MAX


b.INSULATION RESISTANCE: 100 MEGA OHMS MIN

c.DIELECTNIC VOLTAGE: 500V AC ONE MINUTE

d.OPERATING TEMPERATURE: -25°C~ +85°C



PCB Layout Diagram
Top View



③	TERMINAL(-)	1	PHOSPHOR BRONZE, T=0.20	Ni-Plating	
②	TERMINAL(+)	1	PHOSPHOR BRONZE, T=0.20	Ni-Plating	
①	HOUSING	1	PBT UL94 V-0	BLACK	
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR	
COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
DRAWING		TITLE 电池底座适用电池规格CR1220 REV. A			
CHECK					
APPROVAL					
TOLERANCES ARE		PART NO.	LAIL-CR1220-DIP90-B01-1AJ	UNITS mm	
30-150	±0.35				ANGLE
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				
		±3°	DWG.NO.	Projection 	