




ROHS



NOTE:

1.MATERIAL:

a.HOUSING:PA46 UL94 V-0 BLACK

b.CONTACT:SUS304 T=0.35MM



(SURFACE PLATING: Au-PLATING)

SEE ORDERING INFORMATION

2.ELECTRIC:

a.DIELECTNIC VOLTAGE: 500V AC ONE MINUTE

b.OPERATING TEMPERATURE: -10℃~+80℃



PCB Layout Diagram

2	TERMINAL	4	SUS304 T=0.35MM	Au-Plating		
1	HOUSING	1	PA46 UL94 V-0	BLACK		
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR		
COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD				
					DRAWING	
					CHECK	
					APPROVAL	
TOLERANCES ARE		TITLE	18650-电池盒（SMT焊接）	REV.	A	
30-150	±0.35	ANGLE	PART NO.	LAIL-18650-BX2-SMT-1BA	UNITS	mm
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
		±3°	DWG.NO.		Projection	