




线路板安装尺寸示意图




REVISION			
LTR	DESCRIPTION	DATE	APP
A0	NEW RELEASE	05/20/2020	PECK

Specification:

- 1 Current rating: 0.5A Max
- 2 Voltage rating: 30V DC
- 3 Dielectric withstanding voltage: 500V(AC) for 1 min.
- 4 Contact resistance: 100mΩ Max.
- 5 Insulation resistance: 1000MΩ min.
- 6 Temperature range: -25°C~85°C
- 7 Mating cycle: 5000 cycles min
- 8 Insert force: 40N Max
Extraction force: 0.5~40N

邀您使用(微信)小程序
硕方电子开关&连接器选型手册
手机扫码即可进入...



DIMENSION CLASSIFICATION ■ : CRITICAL ☒ : MAJOR			台灣碩方精密電子科技有限公司 TAIWAN SOFNG PRECISION ELECTRONIC CO., LTD							
			TITLE		SOF-DC00790			開關, 连接器 SOFNG		
TOLERANCE TABLE										
.X	±	0.40	PART NO.	DC-079			SERIES	SD106		
.XX	±	0.25	APPROVED	Peck	DWG NO.		SOF-G006			
.XXX	±	0.10	CHECKED	Paul	SCALE	1:1	UNIT	mm	SIZE	A4
ANGLE	±	2°	DRAWIN	David			REV	AO	SHEET NO.	1/1