





ROHS



PCB Layout Diagram
Top View



NOTE:

1.MATERIAL:

- a.HOUSING:PBT UL 94V-0
b.CONTACT:PHOSPHOR BRONZE
(SURFACE PLATING:Sn-PLATING)

SEE ORDERING INFORMATION

2.ELECTRIC:

- a.CONTACT RESISTANCE: 50 MILLIOHMS MAX
b.INSULATION RESISTANCE: 100 MEGA OHMS MIN
c.DIELECTNIC VOLTAGE: 500V AC FOR ONE
MINUTE
d.OPERATING TEMPERATURE: -25°C~ +85°C



3.PACKAGING:

- a.BLISTER TRAY PACKAGING (SEE PAGE TWO FOR
DETAILS)

3	TERMINAL(-)	1	PHOSPHOR BRONZE, T=0.20mm	Sn-Plating
2	TERMINAL(+)	1	PHOSPHOR BRONZE, T=0.40mm	Sn-Plating
1	HOUSING	1	PBT UL94 V-0	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR

COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司			
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
CHECK					
APPROVAL					
TOLERANCES ARE		TITLE	电池座适用于电池规格CR2032	REV.	A
30-150	±0.35	PART NO.	LAIL-CR2032-DIP90-B03-1AK	UNITS	mm
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				
ANGLE		DWG.NO.			
±3°					


REV.	ECN NO.	DESCRIPTION	DRAW	DATE




Packaging information:

1. Each plate contains 10 rows, each row contains 10 PCS, for a total of 100 PCS;
2. 15 plastic trays are bundled together, with an empty plastic tray at the top, totaling 1500 products;
3. Each large plastic bag contains 30 plates of products, totaling 3000 products;
4. Each outer box contains a large plastic bag, totaling 3000 products
5. Seal the top and bottom of the outer box with adhesive tape to form the character "工";

Seal the top and bottom of the outer box with adhesive tape to form the character "工".



desiccant 3PCS



COSTOMTER DRAWING			 深圳市莱联电子有限公司			
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO., LTD			
CHECK						
APPROVAL						
TOLERANCES ARE			TITLE	电池座适用于电池规格CR2032	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-CR2032-DIP90-B03-1AK	UNITS	mm
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
			DWG.NO.		Projection	