




ROHS



PCB Layout Diagram
TOP View

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

NOTE:

1.MATERIAL:

a.HOUSING:PA46 UL94 V-0 BLACK

b.CONTACT: SUS304 T=0.35MM


(SURFACE PLATING: Au1u")

SEE ORDERING INFORMATION

2.ELECTRIC:

a.DIELECTRIC VOLTAGE: 500V AC ONE MINUTE

b.OPERATING TEMPERATURE: -25°C~ +85°C



3	TERMINAL(+)	1	SUS304 T=0.35MM	Au(1u")-Plating
2	TERMINAL(-)	1	SUS304 T=0.35MM	Au(1u")-Plating
1	HOUSING	1	PA46 UL94 V-0	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR

COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司			
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
CHECK						
APPROVAL						
TOLERANCES ARE						
30-150	±0.35	ANGLE	TITLE		REV.	A
10-30	±0.2		PART NO.		UNITS	mm
5-10	±0.15		DWG.NO.		Projection	
0-5	±0.1					