





ROHS



PCB Layout Diagram
Bottom View

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

NOTE:

1.MATERIAL:

01.HOUSING:PA66 BLACK UL94 V-0

02.CONTACTS:STAINLESS STEE(SUS304) 0.3T


(SURFACE PLATING: Ni 100-120u")

SEE ORDERING INFORMATION

2.ELECTRIC:

01.DIELECTNIC VOLTAGE: 500V AC ONE MINUTE

02.OPERATING TEMPERATURE: -25° C~ +85° C



③	TERMINAL -	1	STAINLESS STEE(SUS304)T=0.3mm	Ni-Plating
②	TERMINAL +	1	STAINLESS STEE(SUS304)T=0.3mm	Ni-Plating
①	HOUSING	1	PA66 UL94 V-0	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR

COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司		
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO.,LTD		
CHECK				
APPROVAL				
TOLERANCES ARE				
30-150	±0.35	ANGLE		
10-30	±0.2			
5-10	±0.15			
0-5	±0.1	±3°		
TITLE		电池盒适用电池规格CR123A	REV.	A
PART NO.		LAIL-CR123A-BX-DIP90-1CJ	UNITS	mm
DWG.NO.		Projection		