





剖面 A-A



Rating :

15A 250V AC UL cUL

10A 250V AC VDE 3C KC

Insert And Extract Force:1.36kgf~6.8kgf

Terminal Strength: $\geq 60\text{N}$

Operating Life: ≥ 6000 cycles

Withstand Voltage:Between all terminals:

2500VAC (50-60Hz) 1min

terminals to Base:



3750V AC (50-60Hz) 1min

Leakage Current: 1mA

Insulation Resistance: $\geq 100\text{M}\Omega$ 500V DC

Body Materil:PC 94V-0²

代号	规格
X	1.2
	1.5
	2.0



PANEL CUL-OUT

3	DB-14-FS插销	黄 铜	镀 锡	2	
2	DB-14-FL插销	黄 铜	镀 锡	1	
1	DB-14-5F-RS基座	环阻PC	黑 色	1	
序号	名 称	材 料	处 理	数 量	备 注

			GENERAL TOLERANCE	制 图 DRAWING	 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD				
			DIM TOL	审 核 CHECK					
			X. X ±0.30	批 准 APPROVAL	产品名称 TITLE	DB-14(电源插座)	版 本 REV.	A	
1	初版发行		X. XX ±0.20	比 例 SCALE	产品料号 PART NO.	DB-14-5F-RS	单 位 UNITS	mm	
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	X. XXX ±0.10	投 影 Projection	材 料 MATERIAL		页 次 SHEET	1/1	
			Angle ±3.0°						

深圳市华灿天禄电子有限公司

ShenzhenhuacantianluELECTRONICS CO.,LTD