



P. C. B Layout

技术要求:

Technical requirement

一. 电气性能:

electrical performance

1-1. 额定电流: 3A AC DC.

rated current: 3A AC DC.

1-2. 接触电阻: $\leq 20\text{m}\Omega$

Contact resistance: $\leq 20\text{m}\Omega$

1-3. 绝缘电阻: $\geq 1000\text{M}\Omega$

Insulation resistance: $\geq 1000\text{M}\Omega$

1-4. 耐压: 550V AC/Minute

withstand voltage: 550V AC/Minute

二. 物理特性:

Physical characteristics

2-1. : 环境温度: $-55^{\circ}\text{C} \sim 105^{\circ}\text{C}$

environmental temperature: $-55^{\circ}\text{C} \sim 105^{\circ}\text{C}$

2-2. 焊接温度: $+230^{\circ}\text{C}$, 10s max

welding temperature: $+230^{\circ}\text{C}$, 10s max

三. 材质:

Material

3-1. 塑胶: PBT(Black) UL94V-0

plastic: PBT(Black) UL94V-0

3-2. 插针: 黄铜

contact pin: Brass/Gold plated

注: n为产品PIN位数

浙江博穆精密电子有限公司

未注明公差 Tolerance				Product Chain			
				2.54-1xNA-H2.5-L11.2			
Dwg No				2.54-1xNA-H2.5-L11.2			
XX.	± 0.40	XX.*	$\pm 2^{\circ}$	Drawer	Y.K	Scale	1:1
X.	± 0.30	.XX*	$\pm 1^{\circ}$	Sign	Sun	Unit	MM
.X	± 0.20			Approve	Sun		
.XX	± 0.15						