

RoHS

REV.

ECN.#

DESCRIPTION

NAME

DATE

A0

NEW RELEASE

XieYun

2023.05.24

NOTES

MATERIAL

1. HOUSING MATERIAL : PA9T BLACK UL94V-0.
2. CONTACT MATERIAL : PHOSPHOR BRONZE T=0.3mm.
3. PLATING : Au PLATING ON CONTACT AREA, AND TIN PLATING ON SOLDER AREA OVER NICKEL.
4. SHIELD : 0.20mm THICKNESS COPPER ALLOY WITH NICKEL PLATED.

ELECTRICAL

1. VOLTAGE RATING : 125 VAC RMS.
2. CURRENT RATING : 1.5 AMP.
3. CONTACT RESISTANCE : 40 MILLIOHMS MAX.
4. INSULATION RESISTANCE : 500 MEGOHMS MIN @ 100V DC .
5. DIELECTRIC DIELECTRIC RESISTANCE : 500V DC RMS 50Hz. 1MIN.


MECHANICAL


1. DURRABILITY : 750 CYCLES MIN.
2. MATING/UNMATING FORC: 2.24 KG.F MAX.

ENVIRONMENTAL:

1. OPERATION : -40℃~+85℃.
2. STORAGE : -40℃~+85℃.


Connector Outline



MILLIMETERS	INCH	 东莞市金比莱五金塑胶科技有限公司 DONGGUAN JBL TECH CO., LTD			
X.* ±2*	X.* ±2*				
X ±0.30	.X ±0.012				
.XX ±0.20	.XX ±0.008				
.XXX ±0.10	.XXX ±0.004				
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd		TITLE	RJ45 8P8C 板上型内弯脚带灯扁针		DR
		PART NO.	109014662		CHKD
		PRO J.	PAGE	1/2	UNITS mm
			SIZE	A4	SCALE 1:1
			DIS NO.		


RoHS

USER DIRECTION OF UNREELING



NOTES

1. NUMBER OF CONNECTORS: 250PCS/REEL
2. LEAD TAPE LENGTH



3. QUANTITY: 2500PCS/CARTON

COVER TAPE PEELING ANGLE: 165°~180°

PEELING FORCE: 20~130g

CARRIER TAPE

USER DIRECTION OF UNREELING

DETAIL B


10-REEL

4- TRIANGLE PARTITION

CARTON
390*390*380

TAPE ON

LABEL



MILLIMETERS	INCH
X.* ±2°	X.* ±2°
X ±0.30	.X ±0.012
.XX ±0.20	.XX ±0.008
.XXX ±0.10	.XXX ±0.004

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd
COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd



东莞市金比莱五金塑胶科技有限公司
DONGGUAN JBL TECH CO., LTD

TITLE	RJ45 8P8C 板上型内弯脚带灯扁针		DR		
PART NO.	109014662		CHKD		
PRO J.	PAGE	2/2	UNITS	mm	APPD
SIZE	A4	SCALE	1:1	DIS NO.	