RoHS

REV.	EC#	DESCRIPTION	DATE	DRAWING	CHECKED	APPROVED
A0		NEW RELEASE	07/12'21	JX	/	MOON


12.50
5.00
15.00±0.15



SPECIFICATIONS:

1. ELECTRICAL CHARACTERISTICS
   - 1-1. CURRENT RATING: 0.5 AMP
   - 1-2. VOLTAGE RATING: 40 V
   - 1-3. CONTACT RESISTANCE: 30MILLIOHMS MAX
   - 1-4. INSULATION RESISTTANCE:100M MIN.@500V DC
   - 1-5. DIELECTRIC WITHSTANDING VOLTAGE: 500V AC FOR 1 MINUTE
2. MECHANICAL CHARACTERISTICS:
   - 2-1. INSERTION FORCE : 4.5KGF MAX.
   - 2-2. WITHDRAWING FORCE : 1KGF ~ 4KGF.
3. LIFE TEST: 10000 CYCLES
4. OPERATING TEMPERATURE: -25° C TO +85° C


14.00 +0.05 -0.04
10.80±0.1
Pin2
Pin18
3.37
0.90±0.05
4.55 +0.05 -0.04
0.50
Pin1
9.00
Pin19
18.30±0.25


8.40
1.60
1.80
3.90
4-1.70
4.50
5.38
11.60

PART No.:

105410802

HDMI SERIES
PLATING:
41:G/F+BRIGHT TIN
SERIAL NO.
PAKING:
1: REEL


Pin1
Pin19
1.55
Pin2
Pin18
8.00
9.00


PCB END
15.50 +0.10 -0.00
9.25
7.53
6.30 +0.15 -0.00
2.15
0.50
PIN19
PIN1
5.38
1.55
4-2.10
4-2.70
1.00
8.00
9.00
PIN2
PIN18
4-0.80
4-1.40
⌀0.55±0.03
0.05 C

RECOMMENDED P.C.B LAYOUT
(TOLERANCE=±0.03mm)

SHELL	1	C2680R-H Ni T=0.5MM, 50u"MIN.NICEL ALL OVER
TERMINAL	19	C2680R-H G/F;BRIGHT TIN
HOUSING	1	LCP E130i UL94V-0 BLACK
PART NAME	QTY	MATERIAL PLATING & COLOR

MILLIMETERS	INCH
X.° ± 2°	X.° ± 2°
.X ±0.38	.XX ±0.015
.XX ±0.25	.XXX ±0.010
.XXX± 0.15	.XXXX ±0.006

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF **DongGuan JinBiLai Metal Plastic Technology Co.,Ltd** COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF **DongGuan JinBiLai Metal Plastic Technology Co.,Ltd**

UNITS: MM
MAT'L: SEE NOTES
FINISH: SEE NOTES
QTY: SEE NOTES

东莞市金比莱五金塑胶科技有限公司
DongGuan JinBiLai Metal Plastic Technology Co.,Ltd

PART NUMBER: 105410802
TITLE: HDMI反向沉板式铜壳镀镍四K脚四反弹片
APPD:
CHKD:
DR:
DWG NO.: C-105410802-00

SCALE	SHEET	REV.
1:1	1/2	A0

RoHS


User Direction of Unreeling
16.00±0.10
4.00±0.10
2.00±0.10
1.75±0.10
Φ1.50+0.10/-0.00
32.00±0.30
28.40±0.10
COVER TAPE PEELING ANGLE:165° ~180°
PEELING FORCE:20~130g
CARRIER TAPE
User Direction of Unreeling
Φ100
Φ330
DETAIL B
1.90±0.40
120.00°
10.50
Φ13.00
DETAIL B

NOTES

1. NUMBER OF CONNECTORS:600PCS/REEL
2. LEAD TAPE LENGTH


COVER TAPE
(300mm Min)
PART600PCS
COMPONENT
SUPPLIER
LEADER 240mm MIN
TRAILER
240mm MIN

3. QUANTITY:3600PCS/CARTON


CARTON
4-TRIANGLE PARTITION
6-REEL
TAPE ON
LABEL

MILLIMETERS	INCH
X.° ± 2°	X.° ± 2°
.X ±0.38	.XX ±0.015
.XX ±0.25	.XXX ±0.010
.XXX± 0.15	.XXXX ±0.006

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF **DongGuan JinBiLai Metal Plastic Technology Co.,Ltd** COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF **DongGuan JinBiLai Metal Plastic Technology Co.,Ltd**

UNITS: MM

MAT'L: SEE NOTES

FINISH: SEE NOTES

QTY: SEE NOTES

东莞市金比莱五金塑胶科技有限公司
DongGuan JinBiLai Metal Plastic Technology Co.,Ltd

PART NUMBER: 105410802	TITLE: HDMI反向沉板式铜壳镀镍四K脚四反弹片
APPD:	DWG NO.: C-105410802-00
CHKD:	SCALE: 1:1 / SHEET: 2/2 / REV.: A0
DR:	