






CATEGORY	DESCRIPTION	P/N #
CONNECTOR	RJ45 180度插板带灯带壳H=12.9mm	MJ882-BX11-HXPDLX1

变更料号由原 MJ882-BX11-HXPDLX1
变更为 MJ882-BX11-HXPDLX1

REV.	ECN NO	DESCRIPTION	REVISED	DATE
A03	—	新增塑胶材质选项	XHY	2017.11.18
A04	—	新增LED灯选项	YST	2020.1.10




- SPECIFICATION**
- VOLTAGE RATING: 125 VAC RMS.
 - CURRENT RATING: 1.5 AMP
 - CONTACT RESISTANCE: 40 mΩ MAX
 - INSULATION RESISTANCE: 500MΩ MIN.
 - WITHSTAND VOLTAGE: AC500V RMS 50Hz or 60Hz MIN.
 - OPERATING TEMPERATURE: -40℃~+80℃



X	Terminal Plating
0	Au 1u" Plating
1	Au 3u" Plating
2	Au 6u" Plating
3	Au 15u" Plating
4	Au 30u" Plating

MJ882-BX11-HXPDLX1

X	LED-L
1	GREEN
2	YELLOW
4	Orange/Green
F	YELLOW/GREEN



Recommend PCB Layout
(Jack Top View)
Tolerance: ±0.05mm
Recommend PCB Thickness: 1.6mm

X	塑胶材质
P	PBT
L	LCP
9	PA9T

NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR	Remark
f	LED-R	1	See Table 1	Tin PLATING	
e	LED-L	1	See Table 1	Tin PLATING	
d	SHELL	1	BRASS T=0.2mm	Ni PLATING	
c	TERMINAL	8	PHOSPHOR BRONZE T=0.35mm	Au/Tin PLATING	
b	INSERT	1	See Table 2	BLACK	
a	HOUSING	1	See Table 2	BLACK	

UNLESS OTHERWISE
SPECIFIED TOLERANCES

**东莞市合陵电子有限公司**
DongGuan Heling Electronic Co.,LTD

DECIMALS:	ANGLES:	SCALE: 1/1	UNIT: mm	SIZE: A3	PAGE: 1 OF 1	REV: A04	DWG. NO:
X : ±0.5	X : ±2°						
X.X : ±0.3	X.X : ±1°						
X.XX : ±0.2							
APPROVED BY	CHECKED BY	APPROVED BY	CHECKED BY	APPROVED BY	CHECKED BY	APPROVED BY	CHECKED BY
DICK	CYH	DICK	CYH	DICK	CYH	DICK	CYH
CUSTOMER COPY				CUSTOMER COPY			