






RoHS



REV.	ECN.#	DESCRIPTION	NAME	DATE
A0		NEW RELEASE	liuhongping	2023.01.02
A1		换新图框	huangzipeng	2024.06.20

NOTES:

1. MATERIAL:

1.1 HOUSING: PBT; COLOR: BLACK

1.2 TERMINAL: C51000 $\varnothing 0.45\text{mm}$

1.3 SHELL: C2680

2. FINISH:

2.1 TERMINAL: G/F PLATED ON CONTACT AREA;

G/F PLATED ON SOLDER AREA;

Ni 30u" MIN. UNDERPLATED OVERALL.

2.2 SHELL: Ni 30u" MIN. PLATED OVERALL

2.3 LED: Tin 60u" MIN. PLATED OVERALL.

3. ELECTRICAL SPECIFICATION:

3.1 LOAD RATING: 125VAC, 1.5A;

3.3 CONTACT RESISTANCE: 30m Ω MAX(INITIAL). 40m Ω

MAX (AFTER).

3.4 INSULATION RESISTANCE: 500M Ω MIN.

3.5 DIELECTRIC WITHSTANDING VOLTAGE: 1000V AC.

4. MACHINERY SPECIFICATION:


4.1 DURABILITY: 750 CYCLES MIN.

5. ENVIRONMENTAL SPECIFICATION:

5.1 OPERATING CONDITION: TEMPERATURE -40°C~+85°C;
HUMIDITY 80% R.H MAX


5.2 SALT SPRAY: 24H

6. SOLDER ABILITY: 245±5°C, 5±0.5s

RECOMMENDED PCB LAYOUT
TOP VIEW (COMPONENT SIDE)

MILLIMETERS	INCH	 东莞市金比莱五金塑胶科技有限公司 DONGGUAN JBL TECH CO., LTD			
X" ± 2 "	X" ± 2 "				
X ± 0.30	.X ± 0.012	TITLE RJ45 90度8P8C无弹带灯 13.1H(左绿右黄)			
XX ± 0.20	.XX ± 0.008				
XXX ± 0.10	.XXX ± 0.004	PART NO. 409412931			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd		PRO J.	PAGE 1/2	UNITS mm	APPD
		SIZE	A4	SCALE 1:1	DIS NO.

RoHS



作 业 说 明

1. 根据物料清单备好所需包材；
2. 接上工序所传已做好之产品以水平放置统一方向放入吸塑盒内。 如图所示，每盘吸塑盒内放 100PCS；
3. 将放满产品的吸塑盒底用盒盖叠放吻合，每10盘一叠，一箱2叠
4. 外箱用胶布工字型封箱，并在外箱贴上相应标签

注 意 事 项

1. 吸塑盒内产品不可多装，少装，方向须做到一致；
2. 有未装满之纸箱须使用泡棉或其它不影响品质之物品填充且在纸箱麦头或标签上注明尾数；
3. 确认所使用包材无钉或铁扣之类连接；

100	20	2000PCS	--KG	--KG
PCS/ TRAY	TRAY/ CARTON	QUANTITY	GROSS WEIGHT	NET WEIGHT

MILLIMETERS		INCH		 东莞市金比莱五金塑胶科技有限公司 DONGGUAN JBL TECH CO., LTD				
X." ±2"	X." ±2"	X." ±2"	X." ±2"					
X ±0.30	.X ±0.012	.X ±0.012	.X ±0.012	TITLE RJ45 90度8P8C无弹带灯 13.1H(左绿右黄)				
XX ±0.20	.XX ±0.008	.XX ±0.008	.XX ±0.008	PART NO. 409412931				
XXX ±0.10	.XXX ±0.004	.XXX ±0.004	.XXX ±0.004	CHKD				
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd				PRO J.		APPD		
				PAGE	2/2	UNITS	mm	
				SIZE	A4	SCALE	1:1	DIS NO.