



RoHS

REV.	EC#	DESCRIPTION	DATE	DRAWING	CHECKED	APPROVED
A0		NEW RELEASE	07/12'16	HUANGTAO		YZZ



NOTES:

MATERIAL

- 1.HOUSING MATERIAL :PBT UL94V-0.BLACK
2.CONTACT MATERIAL :C5191
3.SHELL MATERIAL :C2680
4.PLATING :GOLD PLATING OVER NICKEL.

ELECTRICAL:

- 1.VOLTAGE RATING :125 VAC RMS.
2.CURRENT RATING :1.5 AMP.
3.CONTACT RESISTANCE :30 MILLIOHMS MAX.
4.INSULATION RESISTANCE :500 MEGOHMS MIN @ 500V DC .
5.DIELECTRIC WITHSTANDING RESISTANCE :500V AC RMS 50Hz. 1MIN.

MECHANICAL:



- 1.DURRABILITY :750 CYCLES MIN.
2.PCB RETENTION PRE-SOLDER :1 LB MIN.

ENVIRONMENTAL:


1. STORAGE : -40℃~+85℃

PART No.:

RJ SERIES 109010381
PLATING: 1: TRAY
01:G/F+TIN SERIAL NO.



RECOMMENDED P.C.B LAYOUT
TOP VIEW (COMPONENT SIDE)




pin	Name	Description
U1	VCC	+5 VDC
U2	D-	Data -
U3	D+	Data +
U4	GND	Ground

PIN	Name	Description	MILLIMETERS	INCH	UNITS	MM
P1	TX+	Transceive Data+(发信号+)	X. [°] ± 2'	X. [°] ± 2'	MAT'L	
P2	TX-	Transceive Data-(发信号-)	.X ±0.38	.XX ±0.012	SEE NOTES	
P3	RX+	Receive Data+(收信号+)	.XX ±0.25	.XXX ±0.008	FINISH	
P4	N/C	Not connected(空脚)	.XXX±0.15	.XXXX±0.004	SEE NOTES	
P5	N/C	Not connected(空脚)			QTY	
P6	RX-	Receive Data-(收信号-)			SEE NOTES	
P7	N/C	Not connected(空脚)				
P8	N/C	Not connected(空脚)				



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd	
--	--

东莞市金比莱五金塑胶科技有限公司 DongGuan JinBiLai Metal Plastic Technology Co.,Ltd	
PART NUMBER: 109010381	TITLE: RJ45+单层USB2.0 无弹
APPD:	DWG NO.: C-109010381-00
CHKD:	SCALE 1:1
DR:	SHEET 1/2
	REV. A0


RoHS




50 PCS/盒



5盒/叠





2叠



TAPE

贴标签处

环保标签



要求:

1. 真空盒295*220*30mm, 不可有破损, 50PCS/盒.
2. 纸箱465*320*175mm, 材质: K=K, 不可有破损.
3. 将装好产品的5个真空盒整齐叠放在一起, 共两叠500PCS, 放入纸箱中, 用封箱胶纸封好纸箱.

MILLIMETERS	INCH	UNITS	MM	 东莞市金比莱五金塑胶科技有限公司 DongGuan JinBiLai Metal Plastic Technology Co.,Ltd	
X° ± 2°	X° ± 2°	MAT'L		PART NUMBER:	TITLE:
.X ± 0.38	.XX ± 0.012	SEE NOTES		109010381	RJ45+单层USB2.0 无弹
.XX ± 0.25	.XXX ± 0.008	FINISH		APPD:	DWG NO.:
.XXX±0.15	.XXXX±0.004	SEE NOTES		CHKD:	C-109010381-00
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd			QTY	DR:	SCALE
			SEE NOTES		1:1
					SHEET
					2/2
					REV.
					A0