






STRUCTURE (构造)

NO.	ITEM (项目)	SPECIFICATION (规格)		
1	INSULATION (胶膜)	印字膜:通用版20624 (43μm)		
		白膜:80° C 60V (43μm)		
2	SUPPORTING TAPE (补强板)	225μm		Blue (蓝色)
3	CONDUCTOR (导体)	Thickness (厚度)	0.035	±0.005
		Width (宽度)	0.65	±0.03
4	CONDUCTOR (导体镀层)	PLATED (电镀)	锡Sn (1μm)	MIN
		PLATED (电镀)		

DIMENSION (尺寸)

No. of conductors (导体数目)	N	(N) P	
Pitch (间距)	P	1.0	±0.08
Span (总间距)	SP	(N-1)*1	±0.1
Width (总宽度)	W	(N+1)*1	±0.12
Margin (边缘宽度)	M	1.0	±0.12
Total length (总长度)	TL	(TL)	±2.0
Insert Thickness (插接端厚度)	T	0.3	±0.05
Surface Thickness (线身厚度)	ST	0.12	±0.03
Strip Length (裸铜长度)	S1	4.0	4/3可定做 ±0.5
	S2	4.0	4/3可定做 ±0.5
Supporting Tape Length (补强板长度)	B1	6.0	8/6/5/4/可定做 ±1.0
	B2	6.0	8/6/5/4/可定做 ±1.0



技术要求:

- 保存环境: 温度15~25℃ 湿度: 30~50RH%
- 保质期: 镀金: 12个月 镀锡: 6个月
- 产品符合RoHS 2.0标准

DESIGN:	Xiping Huang				广东国连电子有限公司			
CHECK:	Ke Tian				GUANGDONG GUOLIAN ELECTRONICS CO., LTD			
APPROVED:	Youquan Xu			TITLE:				
DIM	TOL	DIM	TOL	FFC CABLE A型				
X.	±0.25	X°	±3.0°	PART NO.				
X.X	±0.20	X.X°		1. 0*NP*TL*A (3/3/5/5) (0.035*0.65)				
X.XX	±0.15	X.XX°		REV. A	SCALE: N/A	UNIT: mm	SHEET: 1/1	
X.XXX		X.XXX°						