

RoHS

焊脚尺寸以顺畅过孔规为准

| REV. | EC# | DESCRIPTION | DATE     | DRAWING | CHECKED | APPROVED |
|------|-----|-------------|----------|---------|---------|----------|
| A0   |     | NEW RELEASE | 11/18'20 | SY      | /       | MOON     |
|      |     |             |          |         |         |          |

#### NOTES

##### MATERIAL

1. HOUSING MATERIAL : GLASS FILLED POLYESTER UL94V-0.
2. CONTACT MATERIAL : PHOSPHOR BRONZE  $\varnothing 0.46\text{mm}$ .
3. PLATING : GOLD FLASH PLATING OVER NICKEL.
4. SHIELD : 0.20mm THICKNESS COPPER ALLOY WITH NICKEL PLATED.

##### ELECTRICAL

1. VOLTAGE RATING : 125 VAC RMS.
2. CURRENT RATING : 1.5 AMP.
3. CONTACT RESISTANCE : 40 MILLIOHMS MAX.
4. INSULATION RESISTANCE : 500 MEGOHMS MIN @ 100V DC .
5. DIELECTRIC DIELECTRIC RESISTANCE : 500V DC RMS 50Hz. 1MIN.

##### MECHANICAL


1. DURRABILITY : 750 CYCLES MIN.
2. MATING/UNMATING FORCE : 2.24 KG.F MAX.

##### ENVIRONMENTAL:

1. STORAGE :  $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$ .
2. OPERATION :  $0^{\circ}\text{C}$  TO  $70^{\circ}\text{C}$ .

PART No.:

RJ SERIES 109530671  
PLATING: 53:G/F OVER Ni  
PAKING: 1: TRAY  
SERIAL NO.



| MILLIMETERS                                                                                                                                                                                                                    | INCH          | UNITS     | MM        | 东莞市金比莱五金塑胶科技有限公司<br>DongGuan JinBiLai Metal Plastic Technology Co.,Ltd |  |                     |       |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|-----------|-----------|------------------------------------------------------------------------|--|---------------------|-------|
| X° ± 2°                                                                                                                                                                                                                        | X° ± 2°       | MAT'L     |           | PART NUMBER:                                                           |  | TITLE:              |       |
| .X ± 0.30                                                                                                                                                                                                                      | .XX ± 0.012   | SEE NOTES |           | 109530671                                                              |  | RJ45 8P8C B型带弹带灯DIP |       |
| .XX ± 0.20                                                                                                                                                                                                                     | .XXX ± 0.008  | FINISH    |           | APPD:                                                                  |  | DWG NO.:            |       |
| .XXX ± 0.10                                                                                                                                                                                                                    | .XXXX ± 0.004 | SEE NOTES |           | CHKD:                                                                  |  | C-109530671-00      |       |
| THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd. COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd |               |           | QTY       | DR:                                                                    |  |                     |       |
|                                                                                                                                                                                                                                |               |           | SEE NOTES |                                                                        |  | SCALE               | SHEET |
|                                                                                                                                                                                                                                |               |           |           |                                                                        |  | 1:1                 | 1/2   |
|                                                                                                                                                                                                                                |               |           |           |                                                                        |  | REV.                | A0    |

RoHS

一:

- 1) 将成品一一放入包装盘内, 依同一方向放入.
- 2) 包装时, 依图所示. 一个包装盘放置80个成品.
- 3) 盖上托盘上盖. 并在四周订一个订书针.


二:

- 4) 依次往上叠放14盘, 产品方向保持一致, 用PE膜将托盘两边缠绕 (PE膜距托盘边约50mm) 再在托盘中间缠绕成一扎. (缠绕2~3圈, 用力要适当, 不宜过紧或过松)
- 5) 将产品盘放入外箱中. 每箱放1扎. 共个产品盘, 即每箱装2240PCS产品

三:

- 1) 用透明胶将纸箱封实.
- 2) 将标签 (按要求打印好的) 贴在纸箱侧右上方.
- 3) 尾数箱用纸壳或其它填充物填满空间, 或将纸箱割小至刚好装下.
- 4) 在搬运过程中要轻拿轻放.
- 5) 在运输中不可堆放过多, 不可有重压现象.


注: 客户特殊要求请参照业务的出货资料



托盘中盖 托盘底

包1扎

PE 膜




装箱


1扎叠14个成品托盘

一箱放2扎

外箱



封箱



物料标签

透明胶

粘胶长度5~10CM

短边

| 产品   | RJ45 8P8C B型带弹脚灯DIP | 2240     |
|------|---------------------|----------|
| PE 膜 | 宽40厚0.03            | 若干       |
| 透明胶  | W=45                | 若干       |
| 吸塑盘盖 | PVC 295*210         | 28       |
| 吸塑盘底 | PVC 295*210         | 28       |
| 外箱   | 双坑A=A 430*310*255   | 1        |
| 品名   | 规格 (mm)             | 用量 (PCS) |

|                                                                                                                                                                                                                                  |              |           |                                                                        |  |                                                                                                                                                                                                                             |  |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------|-----------|------------------------------------------------------------------------|--|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|
| MILLIMETERS                                                                                                                                                                                                                      | INCH         | UNITS     | 东莞市金比莱五金塑胶科技有限公司<br>DongGuan JinBiLai Metal Plastic Technology Co.,Ltd |  |                                                                                                                                                                                                                             |  |
| X.° ± 2°                                                                                                                                                                                                                         | X.° ± 2°     | MM        | PART NUMBER:<br><br>109530671                                          |  | TITLE:<br><br>HDMI A/F 正向沉板 板上H3.75mm 铜壳带弹片                                                                                                                                                                                 |  |
| .X ± 0.30                                                                                                                                                                                                                        | .XX ± 0.012  | MAT'L     |                                                                        |  |                                                                                                                                                                                                                             |  |
| .XX ± 0.20                                                                                                                                                                                                                       | .XXX ± 0.008 | SEE NOTES | APPD:                                                                  |  | DWG NO.:<br><br>C-109530671-00                                                                                                                                                                                              |  |
| .XXX± 0.10                                                                                                                                                                                                                       | .XXXX± 0.004 | FINISH    |                                                                        |  |                                                                                                                                                                                                                             |  |
| THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF Dongguan JinBiLai Metal Plastic Technology Co.,Ltd<br>COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF Dongguan JinBiLai Metal Plastic Technology Co.,Ltd |              | SEE NOTES | CHKD:                                                                  |  | <div><div></div><div>SCALE</div><div>1:1</div></div> <div><div>SHEET</div><div>2/2</div></div> <div><div>REV.</div><div>A0</div></div> |  |
|                                                                                                                                                                                                                                  |              | QTY       |                                                                        |  |                                                                                                                                                                                                                             |  |
|                                                                                                                                                                                                                                  |              | SEE NOTES | DR:                                                                    |  |                                                                                                                                                                                                                             |  |
|                                                                                                                                                                                                                                  |              |           |                                                                        |  |                                                                                                                                                                                                                             |  |