

RoHS

REV.	EC#	DESCRIPTION	DATE	DRAWING	CHECKED	APPROVED
A0		NEW RELEASE	01/20'21	GM		MOON

NOTES

MATERIAL

1. HOUSING MATERIAL: THERMO PLASTICS UL94V-0. BLACK
2. CONTACT MATERIAL: PHOSPHOR BRONZE T=0.25mm.
3. PLATING: GOLD FLASH PLATING OVER NICKEL.
4. SHIELD: STAINLESS STEEL T=0.15mm. WITH NICKEL PLATED.

ELECTRICAL








1. VOLTAGE RATING: 125 VAC RMS.
2. CURRENT RATING: 1.5 AMP.
3. CONTACT RESISTANCE: 40 MILLIOHMS MAX.
4. INSULATION RESISTANCE: 500 MEGOHMS MIN @ 100V DC .
5. DIELECTRIC DIELECTRIC RESISTANCE: 500V DC RMS 50Hz. 1MIN.

MECHANICAL

1. DURRABILITY: 750 CYCLES MIN.
2. MATING/UNMATING FORCE: 2.24 KG. F MAX.

ENVIRONMENTAL:

1. STORAGE: -40°C ~ +85°C.
2. OPERATION: 0° C TO 70° C.




RECOMMENDED PCB LAYOUT
TOLERANCE ±0.05

PART No.:

RJ SERIES
PLATING:
01: G/F+TIN

109010782

PAKING:
2: REEL
SERIAL NO.



MILLIMETERS	INCH	UNITS	MM	东莞市金比莱五金塑胶科技有限公司 DongGuan JinBiLai Metal Plastic Technology Co.,Ltd			
X° ± 2°	X° ± 2°	MAT'L		TITLE:			
.X ± 0.35	.XX ± 0.014	SEE NOTES		PART NUMBER:			
.XX ± 0.25	.XXX ± 0.010	FINISH		109010782			
.XXX ± 0.15	.XXXX ± 0.006	SEE NOTES		APPD:			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd. COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd				DWG NO.:			
				C-109010782-00			
				CHKD:			
				DR:			
				SCALE			
				1:1			
				SHEET			
				1/2			
				REV.			
				A0			

RoHS

A


B

C

D


E

User Direction of Unreeling





NOTES

1. NUMBER OF CONNECTORS: 250PCS/REEL
2. LEAD TAPE LENGTH



3. QUANTITY: 2500PCS/CARTON

User Direction of Unreeling



MILLIMETERS	INCH	UNITS	MM	东莞市金比莱五金塑胶科技有限公司 DongGuan JinBiLai Metal Plastic Technology Co.,Ltd			
X° ± 2°	X° ± 2°	MAT'L		PART NUMBER:		TITLE:	
.X ± 0.35	.XX ± 0.014	SEE NOTES		109010782		RJ45 8P8C 9.8H沉板5.15有壳无灯 DIP脚	
.XX ± 0.25	.XXX ± 0.010	FINISH		APPD:		DWG NO.:	
.XXX ± 0.15	.XXXX ± 0.006	SEE NOTES		CHKD:		C-109010782-00	
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd. COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd				QTY		DR:	
				SEE NOTES			
						SCALE	SHEET
						1:1	2/2
						REV.	A0