







RoHS



REV.	ECN.#	DESCRIPTION	NAME	DATE
A0		NEW RELEASE	liuhongping	2023.01.02

NOTES:

1. MATERIAL:

1.1 HOUSING: LCP UL94V-0; COLOR: BLACK

1.2 TERMINAL: C5191

1.3 SHELL: C2680

2. FINISH:

2.1 TERMINAL: G/F PLATED ON CONTACT AREA;

Tin 50u" MIN. PLATED ON SOLDER AREA;

Ni 20u" MIN. UNDERPLATED OVERALL.

2.2 SHELL: Ni 20u" MIN. PLATED OVERALL

2.3 LED: Tin 50u" MIN. PLATED ON SOLDER AREA;

Ni 20u" MIN. UNDERPLATED OVERALL.

3. ELECTRICAL SPECIFICATION:

3.1 RATED CURRENT: 1.5A

3.3 CONTACT RESISTANCE: 40mΩ MAX(INITIAL). 50mΩ MAX (AFTER).

3.4 INSULATION RESISTANCE: 500MΩ MIN.

3.5 DIELECTRIC WITHSTANDING VOLTAGE: 500V AC

4. MACHINERY SPECIFICATION:

4.1 MATING FORCE: 22.4N MAX.

UNMATING FORCE: 22.4N MAX.

4.2 DURABILITY: 750 CYCLES MIN.

5. ENVIRONMENTAL SPECIFICATION:

5.1 OPERATING CONDITION: TEMPERATURE -40°C~+85°C;



HUMIDITY 80% R.H MAX

6. SOLDER ABILITY: 245±5°C, 5±0.5s

7. IR REFLOW: THE PEAK TEMPERATURE ON THE BOARD SHALL BE MAINTAINED FOR 10 SECONDS AT 260°C.

RJ45 Pin Assignment:

Pin No.	Name
1	Tranceive Data+
2	Tranceive Data-
3	Receive Data+
4	Not connected
5	Not connected
6	Receive Data-
7	Not connected
8	Not connected



MILLIMETERS	INCH
X* ±2*	X* ±2*
.X ±0.30	.X ±0.012
.XX ±0.20	.XX ±0.008
.XXX ±0.10	.XXX ±0.004

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd
COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd




东莞市金比莱五金塑胶科技有限公司

DongGuan JinBiLai Metal Plastic Technology Co.,Ltd

TITLE	RJ45 9.9H 沉板8.8 DIP 外壳带灯(左黄右绿)载带包装	DR	
PART NO.	109410641-C	CHKD	
PRO J.	PAGE 1/2	UNITS	mm
SIZE	A4	SCALE	1:1
DIS NO.			

RoHS

USER DIRECTION OF UNREELING




COVER TAPE PEELING ANGLE: 165°~180°

PEELING FORCE: 20~130g

CARRIER TAPE


USER DIRECTION OF UNREELING

DETAIL B




NOTES

1. NUMBER OF CONNECTORS: 300PCS/REEL
2. LEAD TAPE LENGTH



3. QUANTITY: 2400PCS/CARTON

CARTON
400*400*320mm

MILLIMETERS		INCH		 东莞市金比莱五金塑胶科技有限公司 DONGGUAN JBL TECH CO., LTD			
X' ±2'	X' ±2'	X' ±2'	X' ±2'				
.X ±0.30	.X ±0.012	.X ±0.012	.X ±0.012	TITLE	RJ45 9.9H 沉板8.8 DIP 外壳带灯(左黄右绿)载带包装	DR	
.XX ±0.20	.XX ±0.008	.XX ±0.008	.XX ±0.008	PART NO.	109410641-C	CHKD	
.XXX ±0.10	.XXX ±0.004	.XXX ±0.004	.XXX ±0.004	PRO J.	PAGE 2/2 UNITS mm	APPD	
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd				SIZE	A4	SCALE	1:1
				DIS NO.			