



B

—Housing Colour
N=Black



1. Rated load: 1A
2. Insulation resistance: 100MΩ min
3. Withstand voltage: 500V AC/min
4. Contact resistance: 50mΩ max
5. Durability cycle: 5,000 Cycles
6. Insertion and extraction force: 3-30N
7. Operating temperature range: -40°C ~ +85°C



RoHS
Compliant
EU RoHS Standards

 品贊科技
www.dg-switch.com

REV: A0	SHEET: 1/1
---------	------------