


RoHS



技术参数: Technical parameters:

线数 Poles :
2~20P

适用线规 Wire range :
AGW 32#~28#

温度范围 Temperature range :
-25℃~+85℃

适用PC板厚度 Applicable PC board thickness:
0.6~1.2 mm

额定电流 Current rating :
1.0A

额定电压 Rated voltage :
125V DC/AC

接触电阻 Contact resistance :
≤20mΩ

绝缘电阻 Insulation resistance :
≥100MΩ

耐电压 Withstand voltage :
500V AC/minute

接触点材质 Contact Material

固定片: 黄铜brass

接触脚: 黄铜brass

塑胶材质: PA9T/LCP UL94V-0

					FG1.25立贴	A	B	C	D
FG1.25立贴	A	B	C	D	FG—1.25LT11A	12.50	15.55	18.25	14.30
FG—1.25LT2A	1.25	4.30	7.00	3.05	FG—1.25LT12A	13.75	16.80	19.50	15.55
FG—1.25LT3A	2.50	5.55	8.25	4.30	FG—1.25LT13A	15.00	18.05	20.75	16.80
FG—1.25LT4A	3.75	6.80	9.50	5.55	FG—1.25LT14A	16.25	19.30	22.00	18.05
FG—1.25LT5A	5.00	8.05	10.75	6.80	FG—1.25LT15A	17.50	20.55	23.25	19.30
FG—1.25LT6A	6.25	9.30	12.00	8.05	FG—1.25LT16A	18.75	21.80	24.50	20.55
FG—1.25LT7A	7.50	10.55	13.25	9.30	FG—1.25LT17A	20.00	23.05	25.75	21.80
FG—1.25LT8A	8.75	11.80	14.50	10.55	FG—1.25LT18A	21.25	24.30	17.00	23.05
FG—1.25LT9A	10.00	13.05	15.75	11.80	FG—1.25LT19A	22.50	25.55	28.25	24.30
FG—1.25LT10A	11.25	14.30	17.00	13.05	FG—1.25LT20A	23.75	26.80	29.50	25.55

TOLERANCE UNLESS OTHERWISE SPEC		SHENZHEN FUGANG TECHNOLOGY CO.,LTD					
BASIC DIMENSION	TOLERANCE	DSND	B	C	2026.07.22	TITLE:PIN HEADER	
>0~3	±0.15	CHKD	Y	H	C	2026.07.22	PART NO:FG-1.25LTNA
>3~10	±0.20	APVD	L	P	J	2026.07.22	
>10~30	±0.25						
>30	±0.30						
		UNIT:mm		SCALE:1:1	SIZE:A4	SHEET:1/1	