




REVISIONS (修正)			
NO. (序号)	DESCRIPTION(描述)	DCN NO.(变更号)	DATE(日期)
D.0	NEW RELEASE		

- otes:
- Characteristics:
- A. Material (材料)
- 1) Housing:High Plastic BLACK (UL94V-0)
- 2) Plunger:brass c3604
- B. Plating (电镀)
- 1) Plunger:Brass,Plating 3u' Au over 50u' Ni.
- C. Electrical (电器性能)
- 1) Operating voltage: 12V Max.
- 2) Opetating current: 3A Max.
- 3) Contact resistance: 30mohm Max. at working height(Quiescence).
- D. Environmental (工作环境)
- 1) Storage and operating temoperature range: -40°C~+70°C
- 2) Humidity range: 10% RH to 90% RH
- 3) Salt spray: 24H
- E. Others (其它)
- 1) The dimensions marked * are critical, Should be checked in production
- 2) RoHS compliant product.

DRAW (设计)	LIAOYI	SCALE (比例)	10 : 1	UNIT (单位)	mm	DRAWING NO. (图号)	KZF05P03UFT1-R
COUNTER SIGN (会签)		SHEET (页数)	1 of 1	PROJECT (视图)		MATERIAL (材质)	Seeing notes (见备注)
AUDIT (审核)		DATE (日期)	2025.4.23	VER (版次)	D.0	TITLE (品名)	Pogo pin
APPROVE (核准)		PLATE (镀层)	Seeing notes(见备注)				
THE UNMARKED TOLERANCE ARE AS BELOW : (未标记的公差)				东莞市柯睿电子有限公司 Dong Guan Corroy Electronics Co, Ltd The information in this document is property of Corroy company and should not be copied or reproduced in any other way, without written permission.			
LENGTH (尺寸)							
ANGLE (角度)							
0~6.0	±0.05mm	0.	±2.0°				
>6~30	±0.10mm	0.0	±1.0°				
>30~120	±0.15mm	0.00	±0.50°				