

4

3

2






1

REVISIONS (修正)

NO. (序号)	DESCRIPTION(描述)	DCN NO.(变更号)	DATE(日期)
D.0	NEW RELEASE		2020.03.13

NOTES:

- Materials:
 - .Housing&Cap: High Temperature Polyester (UL94V-0), Black
 - .Plunger: brass
 - .Barrel: brass
 - .Spring: SUS
 - .Plating:
 - .Plunger: 10 micro-inch minimum Au over 50~100 micro-inch nickel.
 - .Barrel : 5 micro-inch minimum Au over 50~100 micro-inch nickel.
- Electrical:
 - .Rated current & voltage: DC12V,1A.
 - .Contact resistance: 50 mohm maximum at working height(quiessence)
- Mechanical:
 - .Normal force: 25g±8g at Normal working height
 - .Durability: 10,000 cycles(minimum)
- When the current is greater than 1A then need to increase the time delaycircuit(3 second)
- To ensure the best usage,please operate it based on the working height
- .Based on the engineering drawings,shall not exceed the maximum allowed compression
- .RoHS & HF complied product.



RECOMMEND PCB LAYOUT

Layout Tolerance: ±0.05mm

DRAW (设计)	XF. WU	SCALE (比例)	10 : 1	UNIT (单位)	mm	DRAWING NO. (图号)	KZT02P10U001-R
COUNTER SIGN (会签)		SHEET (页数)	1 of 1	PROJECT (项目)		MATERIAL (材料)	Seeing notes (见备注)
AUDIT (审核)		DATE (日期)	2020.03.13	VER (版本)	D.0	TITLE (品名)	Pogo pin
APPROVE (核准)		PLATE (便局)	Seeing notes(见备注)				
THE UNMARKED TOLERANCE ARE AS BELOW :				东莞市柯睿电子有限公司			
LENGTH (尺寸)				Dong Guan KeRui Electronics Co,Ltd			
ANGLE (角度)				The information in this document is property of KeRui company and should not be copied or reproduced in any other way, without written permission.			
0~6.0 ±0.05mm							
>6~30 ±0.10mm							
>30~120 ±0.15mm							