


RoHS



技术参数: Technical parameters:

线数 Poles :
2~20P
适用线规 Wire range :
AGW 32#~28#
温度范围 Temperature range :
-25℃~+85℃
适用PC板厚度 Applicable PC board thickness:
0.6~1.2 mm
额定电流 Current rating :
1.0A
额定电压 Rated voltage :
125V DC/AC
接触电阻 Contact resistance :
≤20mΩ
绝缘电阻 Insulation resistance :
≥100MΩ
耐电压 Withstand voltage :
500V AC/minute
接触点材质 Contact Material
固定片: 黄铜brass
接触脚: 黄铜brass
塑胶材质: PA9T/LCP UL94V-0

				FG1.25卧贴	A	B	C
FG1.25卧贴	A	B	C	FG-1.25WT11A	12.50	15.67	18.80
FG-1.25WT2A	1.25	4.42	7.55	FG-1.25WT12A	13.75	16.92	20.05
FG-1.25WT3A	2.50	5.67	8.80	FG-1.25WT13A	15.00	18.17	21.30
FG-1.25WT4A	3.75	6.92	10.05	FG-1.25WT14A	16.25	19.42	22.55
FG-1.25WT5A	5.00	8.17	11.30	FG-1.25WT15A	17.50	20.67	23.80
FG-1.25WT6A	6.25	9.42	12.55	FG-1.25WT16A	18.75	21.92	25.05
FG-1.25WT7A	7.50	10.67	13.80	FG-1.25WT17A	20.00	23.17	26.30
FG-1.25WT8A	8.75	11.92	15.05	FG-1.25WT18A	21.25	24.42	27.55
FG-1.25WT9A	10.00	13.17	16.30	FG-1.25WT19A	22.50	25.67	28.80
FG-1.25WT10A	11.25	14.42	17.55	FG-1.25WT20A	23.75	26.92	30.05

TOLERANCE UNLESS OTHERWISE SPEC		SHENZHEN FUGANG TECHNOLOGY CO.,LTD					
BASIC DIMENSION	TOLERANCE	DSND	B	C	2026.07.22	TITLE:PIN HEADER	
		CHKD	Y	H	C	2026.07.22	PART NO:FG-1.25WTNA
		APVD	L	P	J	2026.07.22	
		UNIT:mm		SCALE:1:1		SIZE:A4	SHEET:1/1
		UNIT:mm		SCALE:1:1		SIZE:A4	SHEET:1/1