




REV.	EC#	DESCRIPTION	DATE	DRAWN	CHECK	APPROVED
1.00		行发版初	2018-04-22			

Pin	DIM.A	DIM.B	DIM.C
2	4.50	1.50	3.60
3	6.00	3.00	5.10
4	7.50	4.50	6.60
5	9.00	6.00	8.10
6	10.50	7.50	9.60
7	12.00	9.00	11.10
8	13.50	10.50	12.60
9	15.00	12.00	14.10
10	16.50	13.50	15.60
11	18.00	15.00	17.10
12	19.50	16.50	18.60
13	21.00	18.00	20.10
14	22.50	19.50	21.60
15	24.00	21.00	23.10
16	25.50	22.50	24.60

温度范围：-25℃~85℃
额定电压：100V AC/DC
额定电流：1A AC/DC
接触电阻：≤0.02Ω
绝缘电阻：≥500MΩ
耐 压 值：500V AC/minute
适用基板厚度：1.6mm

2	PIN	n PCS	材质:黄铜, 电镀:镀亮锡					
1	Housing	1 PCS	材质:PA66 (UL94V-0), 颜色:本色					
NO.	NAME	Q'TY	DESCRIPTION					
东莞市文章济美电子有限公司								
DRAW :		瞿寿坤	2018-04-22	TITLE: WAFER 1.5ZHA 立式 DIP		DRAW NAME: 5001-ZH0015C-**P1-01-B		
DESIGN:		瞿寿坤	2018-04-22					
CHECK:		胡海萍	2018-04-22	SERIES: 1502 SERIES		DRAW NO.		
APPROVED		胡海萍	2018-04-22	P/N:				
CUSTOMER DRAWING				REV. 1.00	SCALE N/A	UNIT: mm	SHEET: 1/1	

技术要求:

- 1) 材质:见附表;
- 2) 电镀:见附表;
- 3) 塑件表面平整、光洁、无毛刺、气泡、烧焦、变形、浇口无拉伤、多料或缺料等不良现象;
- 4) 端子表面无氧化、电镀不良等现象。

GENERAL TOLERANCES			
DIM	TOL	DIM	DEG
X.		X°.	±3.00°
X.X	±0.35	X.X°	±2.00°
X.XX	±0.25	X.XX°	±1.00°
X.XXX	±0.15	X.XXX°	